

A

Accumulating Fast Timer instruction, 5–42
 Accumulating Timer (TMRA) instruction, 5–42
 Accumulator, 5–69
 Accumulator Instructions, 5–52
 Aliases, 3–31
 Analog IBoxes, 5–230
 Approvals, 2–10
 ASCII Conversion Table, G-2
 ASCII In/Out and PRINT, 4–11
 ASCII Instructions, 5–210
 Auto tuning error, 8–48
 Auto Tuning Procedure, 8–45
 Automatic Trapezoidal Profile, E–47
 Auxiliary Functions, 3–9, A–2
 CPU Configuration, A–5
 EEPROM Operations, A–8
 Handheld Programmer Configuration, A–8
 Password Operations, A–9
 RLL Operations, A–4
 via DirectSOFT32, A–3
 via the Handheld Programmer, A–3
 V-memory Operations, A–4

B

Basic EMC Installation Guidelines, J-4
 Battery Backup, 3–8
 BCD Numbering System, I–5
 Binary Numbering System, I–2
 Bit Override, 9–19
 Boolean Instructions, 5–5, 5–10
 Bumpless Transfer, 8–2, 8–3, 8–13, 8–26, 8–76,
 8–77

C

C Data Type, 3–26
 C-more, I-9
 Cables
 programming, 1–8
 Cascade Control, 8–65
 Tuning, 8–67
 Changing Date and Time, 10–14
 Clock / Calendar Instructions, 5–171
 Combination Networks, 5–7
 Comm Port 2, 3–4
 Comm Ports, configuring, 4–7
 Communication IBoxes, 5–231
 Communications from a Ladder Program, K–13
 Read and Write Interlocks, K–13
 Communications Problems, 9–7
 Communications Protocols, K–3
 Comparative Boolean Instructions, 5–26
 Components, 1–6
 Connecting DC I/O, 2–18
 Connections
 power input, 1–8
 programming device, 1–8
 toggle switches, 1–7
 Contacts in Series, 5–6
 Control Relay Bit Map, 3–36
 Converge Jump instruction, 7–23
 Converge Stage instruction, 7–23
 Convergence Jump instruction, 7–20
 Convergence Stages, 7–19
 Counter Example Using Discrete Status Bits
 instruction, 5–46
 Counter I/O IBoxes, 5–231
 Counter Status Bit Map, 3–38
 CPU Features, 3–2

CPU Operation, 3–12

CPU Setup, 3–5

CPU Specifications, 3–3

CT Data type, 3–27

D

Data Type Mismatch, I-7

Date and Time, 10–14

DC input wiring, 2–23

DC output wiring, 2–24

Diagnostics, 9–2

Dimensions, 2–7

DIN rail mounting, 2–9

DirectNET, 4–9, K-10

DirectNET Port Configuration, 4–10

Discrete Helper IBoxes, 5–230

Discrete Inputs with Filter, E-73

DL06 Error Codes, B-2

DL06 PLCMemory, F-2

DL06 Port Pinouts, K-5

DL06 Port Specifications, K-5

Drum Instruction, 6–12

- chart representation, 6–3

- counter assignments, 6–6

- drum control techniques, 6–10

- event drum (EDRUM), 6–14

- handheld programmer mnemonics, 6–16

- masked event drum (MDRMD), 6–19, 6–21

- overview, 6–8

- powerup state, 6–9

- self-resetting, 6–11

- step transitions, 6–11

- Terminology, 6–2

Drum sequencer programming, 1–11

Duplicate Reference Check, 9–13

E

Edits, Run-time, 9–14

Electrical Noise, 9–10

END Instruction, 9–12

END Statement, 5–5

Error Code Locations, 9–3

Error Codes, 9–4, 9–5

Error Term Selection, 8–33

Errors, 9–2

European Union Directives, J-2

F

Feedforward Control, 8–70

Force I/O, 3–14

Forcing I/O Points, 9–16

Freeze Bias, 8–11, 8–34

Front Panel, 2–5

Fuse protection, 2–11

H

Hexadecimal Numbering System, I-3

High-Speed Counter, E-7

High-speed I/O wiring, 2–25

High-Speed Interrupts, E-64

HSIO Features, E-2

HSIO Operating Mode, E-4

Hysteresis, 8–3, 8–13, 8–36, 8–37, 8–38

I

I/O Configuration, 4–4

I/O type selection, 1–5

Indicators, 9–6

Inductive loads, 2–21

Initial Stage (ISG), 7–22

- Instruction execution times, C-3
 - Instruction index, 5-2
 - Instructions
 - drum, 6-12
 - stage, 7-21
 - stage programming, 7-2
 - Instructions, by category
 - Accumulator / Stack Load, 5-52
 - Bit Operation, 5-120
 - Boolean, 5-10
 - Clock / Calendar, 5-171
 - Comparative, 5-26
 - CPU Control, 5-173
 - Immediate, 5-32
 - Logical, 5-69
 - Math, 5-86
 - Number Conversion, 5-127
 - Table, 5-141
 - Timer, Counter and Shift Register, 5-39
 - Transcendental, 5-118
 - Intelligent Box (IBox) Instruction Index, 5-230
- K**
- K-Sequence, K-10
- L**
- LCD Display Panel, 10-2
 - LCD Installation, 10-3
 - LCD instruction, 10-26
 - LCD Keypad, 10-2
 - LCD Menu Navigation, 10-5
 - Loop Mode, 8-27
 - Loop Table Word Definitions, 8-20
- M**
- Maintenance, 9-2
 - Manual, documentation, 1-2
 - Marine Use, 2-10
 - Math IBoxes, 5-230
 - Memory
 - EEPROM, 1-12
 - FLASH, 1-12
 - Memory IBoxes, 5-230
 - Memory Map, 3-25, 3-32
 - Message Instructions, 5-186
 - Midline Outputs, 5-6
 - MODBUS, 4-9
 - MODBUS RTU Communications, K-14
 - MODBUS RTU Instructions, 5-204
 - Mode 10, E-7
 - Mode 20, E-24
 - Mode 30, E-38
 - Mode 40, E-64
 - Mode 50, E-69
 - Mode 60, E-73
 - Mode Switch, 3-6
 - Motion Control, E-2
 - Mounting Guidelines, 2-7
 - Clearances, 2-8
 - MRX instruction, 4-22
 - MWX instruction, 4-22
- N**
- Network Master, 4-18
 - Network Slave, 4-12
 - Network Specification, 4-8
 - Noise, 9-10
 - Non-volatile V-memory, F-3
 - Not Jump, 7-22
 - Numbering Systems, 3-23

O

Octal Numbering System, I-4

P

Parallel Branches in Series, 5-7

Parallel Elements, 5-7

Parallel Processing, 7-19

Password, 3-11, 10-17

PAUSE Instruction, 9-12

PID

Analog Filter, 8-55

DirectSOFT 5 Filter Intelligent Box
Instruction, 8-57

Error Flags, 8-18

Example Program, 8-72

Loop Modes, 8-3, 8-27, 8-53, 8-54, 8-66

Parameters, 8-32

Setup Alarms, 8-35

Special Features, 8-53

PID Alarms, 8-35

Calculation Overflow/Underflow Error, 8-38

Hysteresis, 8-38

Mode/Alarm Bit Description, 8-23

Monitor Limit, 8-35

Programming Error, 8-38

PV Deviation, 8-36

Rate-of-Change, 8-37

PID Loop

Alarms, 8-13

Auto Tuning, 8-40

Configure, 8-25

Features, 8-2

Manual Tuning, 8-40, 8-41, 8-44, 8-47, 8-55

Mode, 8-27

Operating Modes, 8-14

Operation, 8-9

Program Setup, 8-72

Reverse Acting, 8-12, 8-14, 8-26, 8-40

Setup, 8-18

Terminology, 8-77

Troubleshooting Tips, 8-75

PID Mode 2 Word Description, 8-22

PID Mode Setting 1 Description, 8-21

Port Setup, K-6

Position Algorithm, 8-9, 8-15, 8-78

Position Form, 8-9

Power Budgeting, 4-5

Power supply, 2-12

Product Weight table, H-2

Products and Data Types, I-9

Program Mode, 3-13

Programming Devices, 2-15

Pulse Catch Input, E-69

Pulse Output, E-38

Q

Quick Start, 1-6

R

Ramp/Soak Generator, 8-58

Controls, 8-61

DirectSOFT 5 Ramp/Soak Example, 8-63

Profile Monitoring, 8-62

Ramp/Soak Flag Bit Description, 8-23

Ramp/Soak Table Location, 8-24

Relay Ladder, 8-63

Table, 8-59

Table Flags, 8-61

Test Profile with PID View, 8-64

Testing, 8-62

Rate-of-Change, 8-3, 8-13, 8-14, 8-37

Real Numbering System, I-5

Relay outputs, 2–20
 Remote I/O Bit Map, 3–39
 Reset Windup, 8–10, 8–34, 8–78
 Response Time, 3–17
 Retentive Memory Ranges, 3–10
 RUN Indicator, 9–7
 Run Mode, 3–13
 Run Time Edits, 9–14

S

S Data type, 3–28
 Safety, 2–2
 Emergency Stops, 2–3
 Orderly System Shutdown, 2–4
 Scan Time, 3–20
 Serial Communications, K–2
 RS-232C, K–2
 RS-422, K–2
 RS-485, K–3
 Series Branches in Parallel, 5–7
 Signed vs. Unsigned Integers, I–8
 Simple Rungs, 5–5
 Sinking / sourcing concepts, 2–16
 Slot Numbering, 4–3
 SP Data Type, 3–28
 Special Instructions, 9–12
 Special Relays, D–2
 Special Relays, Error Codes, 9–3
 Specifications, 2–26
 Specifications, environmental, 2–10
 Square Root, 8–14
 Stage Control / Status Bit Map, 3–34
 Stage Counter instruction, 7–17
 Stage instructions, 7–21
 Stage Jump Instruction, 7–7
 Stage Programming, 7–2, 7–15

convergence, 7–19
 emergency stop, 7–14
 four steps to stage programming, 7–9
 garage door opener example, 7–10
 introduction, 7–2
 jump instruction, 7–7
 mutually exclusive transitions, 7–14
 parallel processes, 7–12
 parallel processing concepts, 7–19
 power flow transition, 7–18
 program organization, 7–15
 questions and answers, 7–27
 stage instruction characteristics, 7–6
 stage view, 7–18
 state transition diagrams, 7–3
 supervisory process, 7–17
 timer inside stage, 7–13
 Startup, 9–11
 State Diagram, 7–11
 Status Indicators, 3–6
 Step Transitions, 6–4
 Step Trapezoidal Profile, E–46
 STOP Instruction, 9–12
 Syntax Check, 9–11
 System Design, 1–10

T

T Data Type, 3–26
 Technical Support, 1–2
 Terminal Block Removal, 2–6
 Time-Proportioning Control, 8–68
 On/Off Control Program, 8–69
 Timer (TMR) and Timer Fast (TMRF), 5–40
 Timer Example Using Discrete Status Bits
 instruction, 5–41
 Timer Status Bit Map, 3–38

Index

Timer, Counter and Shift Register
Instructions, 5–39
Transfer Mode, 8–26
Troubleshooting, 9–8, 9–11

U

Up/Down Counter, E-24

V

V Data Type, 3–27
Velocity Algorithm, 8–9, 8–15, 8–78
 Velocity Form, 8–12
V-memory, 3–29

W

Web site, 1–2
Wiring Diagrams, 2–26
 D0–06AA I/O Wiring Diagram, 2–26
 D0–06AR I/O Wiring Diagram, 2–28
 D0–06DA I/O Wiring Diagram, 2–30
 D0–06DD1 I/O Wiring Diagram, 2–32
 D0–06DD1–D I/O Wiring Diagram, 2–38
 D0–06DD2 I/O Wiring Diagram, 2–34
 D0–06DD2–D I/O Wiring Diagram, 2–40
 D0–06DR I/O Wiring Diagram, 2–36
 D0–06DR–D I/O Wiring Diagram, 2–42
Wiring Guidelines, 2–11

X

X Data Type, 3–26
X Input / Y Output Bit Map, 3–33

Y

Y Data Type, 3–26