

# Table of Contents

---

## Chapter 1: Introduction

<b>Manual Overview</b> .....	<b>1-2</b>
The Purpose of this Manual .....	1-2
Supplemental Manuals .....	1-2
Technical Support .....	1-2
Conventions Used .....	1-3
Key Topics for Each Chapter .....	1-3
<b>D0-DCM Overview</b> .....	<b>1-4</b>
Important Configuration Information and PLC Firmware Requirements .....	1-4
Hardware Features .....	1-4
Module Uses .....	1-4
<b>DCM Application Examples</b> .....	<b>1-5</b>
<i>Direct</i> NET Master or Slave .....	1-5
Additional Communications Port .....	1-6
Modbus RTU Master or Slave .....	1-6

## Chapter 2: Installation, Network Cabling and Module Specifications

<b>Inserting the D0-DCM into the PLC</b> .....	<b>2-2</b>
D0-DCM Module Installation .....	2-2
PLC Firmware and <i>Direct</i> SOFT Requirements .....	2-2
<b>Building the Communication Cable</b> .....	<b>2-3</b>
Consideration 1: Physical Configuration .....	2-3
Consideration 2: Electrical Specification RS232 or RS422/485 .....	2-4
Consideration 3: Cable Schematics .....	2-4
Consideration 4: Cable Specifications .....	2-5
Consideration 5: Installation Guidelines .....	2-5
<b>Wiring Diagrams</b> .....	<b>2-6</b>
D0-DCM Port 1 RS-232 Network .....	2-6
D0-DCM Port 2 RS-485 Network .....	2-6
D0-DCM Port 2 RS-422 Network .....	2-7
<b>Module Specifications</b> .....	<b>2-8</b>
General Specifications .....	2-8
Port 1 Specifications .....	2-8
Port 2 Specifications .....	2-9
Status Indicators .....	2-9

## Chapter 3: D0-DCM Module Setup

<b>Important Module Configuration Information</b> .....	<b>3-2</b>
<b>Tip for <i>Direct</i>SOFT5 Users (optional)</b> .....	<b>3-2</b>
<b>Using <i>Direct</i>SOFT5 to Configure the DCM</b> .....	<b>3-3</b>
<i>Direct</i> SOFT5 PLC>Menu>Setup .....	3-3
Select DCM Slot .....	3-3
Port 1 Configuration (slave only) .....	3-4
Port 2 Configuration (slave mode) .....	3-5

---

Port 2 Configuration (DirectNET Master) .....	3-6
Port 2 Configuration (Modbus Master) .....	3-7
Port 2 Configuration (Non-Sequence) .....	3-8
<b>D0-DCM Port Configuration Registers .....</b>	<b>3-9</b>
Module Configuration Registers .....	3-9
Default Communications Parameters .....	3-9
Parameter Descriptions .....	3-10
A: Port 1 – Transmit Mode, Protocol .....	3-11
B: Port 1 – Station Address, Baud Rate, Parity .....	3-12
C: Port 2 – RTS On/Off delay, Transmit Mode, Protocol, Comm Time-out, RS-485 Mode .....	3-13
D: Port 2 – Station Address, Baud Rate, Data Bit, Stop Bit, Parity .....	3-15
E: Port 2 – Character Time-out .....	3-16
F: Port 1 and 2 Setup and Completion Code .....	3-17
G: Port 1 and 2 Reset Time-out .....	3-17
<b>Using Ladder Logic to Setup the D0-DCM (DL05) .....</b>	<b>3-18</b>
Port 1 Example: (This port is a slave only) .....	3-18
Port 2 Example: Slave Mode .....	3-18
Port 2 Example: DirectNet Master .....	3-19
Port 2 Example: MODBUS RTU Master .....	3-19
<b>Using ladder Logic to Setup the D0-DCM (DL06) .....</b>	<b>3-20</b>
Port 1 Example: Slave Mode Only .....	3-20
Port 2 Example: Slave Mode .....	3-20
Port 2 Example: DirectNet Master .....	3-21
Port 2 Example: MODBUS RTU Master .....	3-21
<b>Chapter 4: <i>DirectNet</i> Communications Using RX/WX</b>	
<b>RX / WX Network Instructions .....</b>	<b>4-2</b>
Read (RX) and Write (WX) Instructions .....	4-2
Building the Read (RX) or Write (WX) Routine .....	4-2
The First LD Instruction .....	4-2
The Second LD Instruction .....	4-3
The LDA Instruction .....	4-3
Read (RX) Instruction .....	4-4
Write (WX) Instruction .....	4-4
<b>Addressing the Different Memory Types .....</b>	<b>4-5</b>
Bit Memory .....	4-5
Word Memory and Aliases .....	4-5
DL05 CPU .....	4-6
DL06 CPU .....	4-6
<b>Special Relays for Communications .....</b>	<b>4-7</b>
<b>Program with One RX Instruction .....</b>	<b>4-8</b>
Program for the Master PLC .....	4-8
Program for the Slave PLC .....	4-8
Program for the Master PLC .....	4-9
<b>Program with One WX Instruction .....</b>	<b>4-10</b>
Program for the Master PLC .....	4-10
Program for the Slave PLC .....	4-10
Program for the Master PLC: .....	4-11
Program for the Slave PLC .....	4-11
<b>Integrating Multiple RX and WX Instructions .....</b>	<b>4-12</b>
Interlocking Relays .....	4-12

First RX/WX Instruction .....	4-13
Second RX/WX Instruction .....	4-14
Third RX/WX Instruction .....	4-14
Returning to the First RX/WX Instruction .....	4-14
Shift Register .....	4-15
Store If Equal .....	4-15
First RX/WX Instruction .....	4-16
Second RX/WX Instruction .....	4-16
Third RX/WX Instruction .....	4-16

## Chapter 5: Modbus RTU Communications RX/WX and MRX/MWX

<b>Network Slave Operation</b> .....	<b>5-2</b>
Modbus Function Codes Supported .....	5-2
Determining the Modbus Address .....	5-2
If Your Host Software or Master Requires the Data Type and Address .....	5-3
If the Host Software or Master Requires an Address ONLY .....	5-6
<b>Network Master Operation: RX / WX Instructions</b> .....	<b>5-9</b>
Overview .....	5-9
Modbus Function Codes Supported .....	5-9
PLC Memory Supported for Master Operation .....	5-10
Example 1: Calculating Word PLC Address .....	5-11
Example 2: Calculating Discrete Input PLC Address .....	5-11
Building the Read (RX) or Write (WX) Routine .....	5-12
Step 1: Identify DCM Slot Location and Slave .....	5-12
Step 2: Load Number of Bytes to Transfer .....	5-13
Step 3: Specify Master Memory Area .....	5-13
Step 4: Specify Slave Memory Area .....	5-13
RX / WX Instructions Example .....	5-14
Multiple Read and Write Interlocks .....	5-14
<b>Network Master Operation: DL06 MRX / MWX Instructions</b> .....	<b>5-15</b>
Modbus Read from Network (MRX) .....	5-15
MRX Slave Memory Address .....	5-16
MRX Master Memory Addresses .....	5-16
MRX Number of Elements .....	5-16
MRX Exception Response Buffer .....	5-16
Modbus Write to Network (MWX) .....	5-17
MWX Slave Memory Address .....	5-18
MWX Master Memory Addresses .....	5-18
MWX Number of Elements .....	5-18
MWX Exception Response Buffer .....	5-18
MRX / MWX Example in <i>DirectSOFT5</i> .....	5-19
Multiple Read and Write Interlocks .....	5-19

## Chapter 6: Communications Using Network IBox Instructions

<b>Network Configuration Instruction (NETCFG)</b> .....	<b>6-2</b>
NETCFG (IB-700) .....	6-2
<b>Network Read Instruction (NETRX)</b> .....	<b>6-3</b>
NETRX (IB-701) .....	6-3
<b>Network Write Instruction (NETWX)</b> .....	<b>6-4</b>
NETWX (IB-702) .....	6-4
<b>Example Using NETCFG, NETRX and NETWX</b> .....	<b>6-5</b>