

TABLE OF CONTENTS



Chapter 1: Introduction to the CTRIO Modules

CTRIO Version 2 and Workbench Version 2 New Features	1-2
Expanded I/O Map Implications	1-2
Using CTRIO/Workbench Version 1	1-2
CTRIO Module Overview	1-3
CTRIO Workbench	1-3
CTRIO Functions	1-3
Typical Counter Applications:	1-4
Support Systems for the CTRIO Modules	1-4
H0-CTRIO	1-4
H2-CTRIO	1-4
H4-CTRIO	1-4
T1H-CTRIO	1-4
CTRIO Specifications	1-5
H0-CTRIO LED Indicators	1-7
H2-CTRIO LED Indicators	1-8
H4-CTRIO LED Indicators	1-9
T1H-CTRIO LED Indicators	1-10

Chapter 2: Installation and Field Wiring

Installing the H0-CTRIO Module	2-2
CPU and CTRIO Compatibility Chart	2-2
Sinking Outputs	2-3
Sourcing Outputs	2-3
Jumper Selections	2-3
Setting H0-CTRIO Jumpers	2-3

Wiring the H0-CTRIO Module	2-4
H0- CTRIO Quadrature Encoder Wiring Example	2-5
H0-CTRIO TTL Quadrature Encoder Field Wiring	2-6
H0-CTRIO TTL Input Wiring	2-7
Sinking Outputs Jumper Settings	2-8
Sourcing Outputs Jumper Settings	2-8
H0- CTRIO Output Wiring Schematic	2-8
Sinking Outputs Jumper Settings	2-9
H0-CTRIO Stepper/Servo Drive Wiring Example	2-9
Installing the H2-CTRIO Module	2-10
CPU and CTRIO Compatibility Chart	2-10
Setting H2-CTRIO Jumpers	2-11
Wiring the H2-CTRIO Module	2-12
H2- CTRIO Quadrature Encoder Wiring Example	2-13
H2-CTRIO TTL Quadrature Encoder Field Wiring	2-14
H2-CTRIO TTL Input Wiring	2-15
H2- CTRIO Output Wiring Schematic	2-16
H2-CTRIO Stepper/Servo Drive Wiring Example	2-17
Installing the H4-CTRIO	2-18
CPU and CTRIO Compatibility Chart	2-18
Wiring the H4-CTRIO Module	2-19
H4-CTRIO Quadrature Encoder Wiring Example	2-20
H4-CTRIO TTL Quadrature Encoder Field Wiring	2-21
H4-CTRIO TTL Input Wiring	2-22
H4-CTRIO Output Wiring Schematic	2-23
H4-CTRIO Stepper/Servo Drive Wiring Example	2-24
Installing the T1H-CTRIO	2-25
CPU and CTRIO Compatibility Chart	2-25
Wiring the T1H-CTRIO Module	2-26
T1H-CTRIO Output Field Wiring	2-27
T1H-CTRIO Input Field Wiring	2-27

T1H-CTRIO Quadrature Encoder Wiring Example	2-28
T1H-CTRIO TTL Quadrature Encoder Field Wiring	2-29
T1H-CTRIO TTL Input Wiring	2-30
T1H-CTRIO Output Wiring Schematic	2-31
T1H-CTRIO Stepper/Servo Drive Wiring Example	2-32
PNP Field Device	2-33
NPN Field Device	2-33
Solid State Input Device Wiring to H0/H2/H4/T1H-CTRIO	2-33

Chapter 3: Introduction to CTRIO Workbench

What is CTRIO Workbench?	3-2
Installing CTRIO Workbench	3-2
Getting Started with CTRIO Workbench	3-2
Offline CTRIO Configuration	3-2
Online CTRIO Configuration	3-3
Successful On-line Connection	3-4
Module Modes of Operation	3-5
Program Mode - Configuring the CTRIO Module	3-5
Run Mode - Start Processing I/O Pulses with the CTRIO Module	3-5

Chapter 4: Configuring the Inputs Using CTRIO Workbench

Configure IO Dialog Overview	4-2
Input Function Selections	4-3
Supported Functions	4-3
Discrete Outputs Pre-Assigned to Input Functions	4-3
Counter Function	4-4
Quad Counter	4-5
Pulse Catch	4-6
Edge Timer	4-7
Dual Edge Timer	4-8
Soft Resets	4-9
Reset 1 and Reset 2 (Hard Resets for Counters Only)	4-9

Capture 1	4-10
Inhibit 1	4-10
Introduction to the Scaling Wizard	4-11
Scaling Wizard Examples for Counter Functions	4-11
Position Scaling (Counter)	4-12
Rate Scaling (Counter)	4-13
Using the Scaling Wizard with Timer Functions	4-14
Interval Scaling (Timer)	4-14

Chapter 5: Configuring the Outputs Using CTRIO Workbench

Configure IO Dialog Overview	5-2
Output Function Selections	5-3
Supported Functions	5-3
CTRIO Memory Usage: Pulse Profiles and Preset Tables	5-3
Raw Output	5-4
Discrete Outputs	5-5
Creating and Using the Output Preset Tables	5-6
Using the Discrete Outputs in Level Mode	5-7
Pulse Outputs	5-8
Creating Pulse Output Profile Tables	5-8
Trapezoidal Profile	5-9
S-Curve Profile	5-10
Symmetrical S-Curve Profile	5-11
Dynamic Positioning Profile	5-12
Dynamic Velocity Profile	5-13
Home Search Profile	5-14
Home Search Routines	5-15
Additional Pulse Profiles	5-16

Chapter 6: Program Control

Input (n) Parameter Definitions	6-2
Input Memory Map for Data Transfers from CTRIO to CPU	6-2
Output Status Bit Definitions (Pulse Output)	6-3
Output Status Bit Definitions (for Preset Table Control)	6-3
Input Function Status Bit Definitions	6-3
Output (n) Parameter Definitions	6-4
Output Memory Map for Data Transfers from CPU to CTRIO	6-4
Output (n) Parameter Definitions	6-5
Output Control Bit Definitions (Raw Mode)	6-5
Output Control Bit Definitions (for Preset Table Control)	6-5
Output Control Bit Definitions (Pulse Output)	6-5
Input Function Control Bit Definitions	6-5
System Functions Control Bit Definitions	6-6
System Functions Status Bit Definitions	6-6
I/O Map Dialog	6-7
I/O Map with <i>DirectLogic</i> PLC (2 ranges mode)	6-7
I/O Map with <i>DirectLogic</i> PLC (4 ranges mode)	6-8
I/O Map with EBC/WinPLC	6-9
I/O Map with <i>DirectLogic</i> PLC with CTRIO in ERM/EBC Network	6-9
I/O Map with an H2-PBC or T1H-PBC Profibus DP Controller	6-10
I/O Map with a T1K-DEVNETS DeviceNet Controller	6-11
I/O Map with a T1K-MODBUS Modbus RTU Controller	6-13
Exporting to <i>DirectSOFT</i>	6-14
Printing a Memory Map Report	6-14
Addressing Conventions	6-15
(with V-memory Examples for DirectLOGIC PLCs)	6-15
Example for Bit-accessed Data in PLC CPUs	6-15
Addressing High and Low Byte of Word Parameters	6-15
Addressing High and Low Word of DWord Parameters	6-15
Input Function Status DWord Parameters	6-16
Input Function Status Bit Definitions	6-16
Input Function Control Bit Definitions	6-16

Input Function Status/Control Bits and Parameters	6-16
Control Registers	6-17
Status Registers	6-17
Example Input Control/Status Bits and Parameter Register Addresses	6-17
Memory Mapping Example for D2-240 CPU	6-18
Input Functions	6-19
Counter & Quadrature Counter	6-19
Edge Timer and Dual Edge Timer	6-20
Edge and Dual Edge Timer Timeout Function	6-21
Pulse Catch Input Function	6-22
Runtime Changes to CTRIO Configured Preset Tables	6-23
Entry Number for Edit Table Entry Commands	6-24
Entry Type for Edit Table Entry Commands	6-24
Discrete Outputs Driven from a Scaled level	6-25
Load Preset Table Flowchart	6-26
Pulse Output Status/Control Bits and Command Codes	6-27
Command Code and Parameter Definitions	6-28
Status Bits	6-29
Control Bits/Registers	6-29
Memory Mapping Example for D2-240 CPU	6-30
Pulse Output Profiles	6-31
Trapezoid, S-Curve, Symmetrical S-Curve, Home Search Profiles	6-32
Trapezoid, S-Curve, Symmetrical S-Curve and Home Search Flowchart	6-33
Running a Trapezoid, S-Curve, Symmetrical S-Curve, or Home Search Profile ...	6-34
Dynamic Positioning	6-35
Dynamic Positioning Flowchart	6-36
Dynamic Positioning using the CTRIO Y0 and Y1	6-37
Dynamic Velocity using the CTRIO Y0 and Y1	6-38
Dynamic Velocity	6-38
Dynamic Velocity Mode Flowchart	6-39
Velocity Mode	6-40
Velocity Mode control on CTRIO Y0 & Y1	6-40
Velocity Mode Flowchart	6-41
Run to Limit Mode	6-42
Run to Limit Mode Flowchart	6-43

Run at Velocity on CTRIO Y0 & Y1 until Discrete Input Limit 6-44

Run to Position Mode 6-45

Run to Position Mode Flowchart 6-46

Run at Velocity on CTRIO until Input Function Value Position 6-47

System Functions 6-48

 Reading All CTRIO's Internal Registers Flowchart 6-49

 Writing to All CTRIO's Internal Registers Flowchart 6-50

 Writing to One CTRIO Internal Register Flowchart 6-51

Chapter 7: Using Monitor I/O

Using the Monitor I/O Dialog 7-2

 I/O Status & Input Functions 7-3

 Output Functions 7-4

 System Functions 7-6

Monitor I/O Error Codes 7-7

Chapter 8: DirectLogic Programming Examples

Programming Examples Overview 8-2

Load and Run a Pulse Profile 8-3

Dynamic Positioning 8-4

Dynamic Velocity 8-5

Velocity Mode 8-6

Run to Limit Mode 8-7

Run to Position Mode 8-8

System Functions Examples Overview 8-9

Simulating Retentive Counter 8-10

Reading CTRIO Internal Registers 8-11